

|                                      |                   |
|--------------------------------------|-------------------|
| Weight capacity                      | < 125 kg          |
| Turning circle                       | 90 cm             |
| Adjustable for users between lengths | 160 cm. en 190 cm |
| Width seat                           | 62 cm             |
| Length seat                          | 55 cm             |
| Height from ground to seat           | 57 cm             |
| Length                               | 64 cm             |
| Wheel size                           | 20 cm             |
| Colors                               | Silver and black  |
| Weight                               | 9,5 kg            |
| Material of frame                    | aluminium         |
| Size when folded                     | 85 x 62 x 45 cm   |
| Volume basket                        | 25 liter          |



*Umotions are available for short and tall people*

Patent filed

Name and model are protected

Ask for a try-out period at:

The Umotion is produced by:



**VILLERIUSMEDICAL**

**P.O. BOX 75998  
1070 AZ AMSTERDAM  
THE NETHERLANDS  
0031 (0) 20-6737558  
INFO@VILLERIUSMEDICAL.EU  
WWW.VILLERIUSMEDICAL.EU  
WWW.UMOTION.EU**



The Parkinson's Disease walker  
Developed with U, made for U



- \* Optimal stability because of U-shaped base
- \* Small turning circle
- \* Tension adjustment on wheels for more control
- \* Single handed operating braking system
- \* Curb support for high and low curbs
- \* Antislip seat with loin- and backsupport
- \* For more Unique features: turn page



## Advantages

## Walker

## Umotion

|   |                                     |                                     |
|---|-------------------------------------|-------------------------------------|
| Unique stability                        | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Manouverability < 90 cm                 | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Safely getting up from a chair          | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| One-hand-only operated braking system   | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Reversed braking system                 | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Seat with 3-D antislip coating          | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Curb support for outside & inside       | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Tension control                         | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Adjustable height of handgrips (handle) | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> |
| Loin- and backsupport whilst seating    | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Ergonomic posture support               | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| <b>Options</b>                          |                                     |                                     |
| Green laserlight                        | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Vibrating metronome                     | <input type="checkbox"/>            | <input checked="" type="checkbox"/> |
| Crate, 25 liters                        | <input checked="" type="checkbox"/> | <input checked="" type="checkbox"/> |



## Unique stability

- The U-shaped base provides Unique stability and stimulates a correct body posture

## Manoeuvrability

- The Umotion can also be used in small areas such as the bathroom and kitchen because of the small turning circle (< 90 cm)

## Safely getting up from a chair

- The user will safely get up from a chair with the curb support on the diagonal (inside) level and because the Umotion is on brakes.

## (One-hand-only operated) braking system

- The Umotion will only roll when one or both handbrakes are squeezed; reversed braking system.
- The Umotion stops immediately when the user releases the braking handles.
- The braking system can also be adjusted to a traditional braking system; thus squeezing is braking.

## Seat with with 3-D antislip coating

- The user can be comfortably seated because the Umotion is equipped with a large seat with loin- and backsupport
- The seat is equipped with 3-D antislip coating for safe seating and therefore it can also be used as a tray. See illustration 1

## 1 Curb support

- High and low curbs can be easily taken outside as well as inside the house. See illustration 2
- The wheels at the very end of the frame assists the Umotion over the curbs and avoids tilting.
- High curbs can be taken with the curb support on the horizontal (outside) level.
- Lower curbs can be taken with the curb support on the diagonal (inside) level
- The curb support in the diagonal level offers good assistance to get up from a chair

## 2 Tension control

- The desired resistance can preventatively be adjusted for safe striding support. See illustration 3

## 3 Unfold, fold and store

- The Umotion is easy to unfold and to fold
- When folded, the Umotion is compact for transportation. See illustration 4
- The Umotion can vertically be stored. See illustration 5

## 4 Ergonomical posture

- The handles are pointed seven degrees downwards and seven degrees outwards for an ergonomic posture of the wrists and hands. See illustration 6

## 5 Reflecting stickers

- The Umotion is equipped with reflecting stickers. See illustration 7

## Extra options:

### Green laserlight

- A green laserlight can be used to overcome 'FREEZING'.
- As soon as the user steps over the laserlight, the 'FREEZING' episode is over.
- Green laserlight is 6 times better visible than red laserlight. See illustration 8

### Vibrating metronome

- The metronome is adjustable in tactile frequency and volume. See illustration 9

### Crate

- The wide U-shaped base is suitable for a crate with a volume of 25 litres.